



Data Sheet: Cleaning Strategy
Document Title: CSO&M Data Sheet
Document Number: 001
Document Issue Date: Sept 11

Kwik-klik

FAST FIT TEMPORARY HOARDING SYSTEMS

ecogenikTM

100% recycled hoarding panels

NOTES

Cleaning Strategy & Maintenance Data Sheet for all Kwik-Klik, Hygienik and Ecogenik products.

Hygienik, Kwik-Klik and Ecogenik Cleaning Systems

All products can be readily cleaned by regularly washing with copious quantities of water or diluted soap/detergent solutions. The latter has the added advantage of making the PVC surface temporarily anti-static.

We also supply multi-purpose cleaning wipes that are quick, convenient and highly effective for Hygienik, Kwik-Klik and Ecogenik products. These will remove silicone PU Foam, most adhesives, paints, oils and grease from surfaces, hands and tools. Wipes are supplied in containers of 80 wipes, 20cm x 30cm.

Proprietary cleaners should NOT be used unless specifically stated to be suitable because they contain an abrasive or a solvent that could adversely affect the PVC surface. The materials may be pressure cleaned for sterilisation purposes.

The recommended maximum continuous working temperature of Hygienik and Kwik-Klik products is 60 degrees Celsius/140 Fahrenheit.

© Copyright 2011 Kwik-Klik Hoardings Ltd
Kwik-Klik Hoardings Ltd, Unit 3a, A1 Business Park,
370 Bradford Road, Brighouse, West Yorkshire, HD6 4DJ

For Further Technical Advice:
Telephone: 01484 717192
Email: tony@kwik-klik.co.uk
www.kwik-klik.co.uk www.ecogenik.co.uk

© Copyright 2011 Hygienik Systems Ltd
Hygienik Systems Ltd, Unit 3a, A1 Business Park,
370 Bradford Road, Brighouse, West Yorkshire, HD6 4DJ

For Further Technical Advice:
Telephone: 01274 355777
Email: matt@hygienee.com
www.hygienee.com